

SR55-SPLT Cut Sheet



Stellar SR55 series communication splitter, 3 ports, (3) RS-485 (RJ45) female port(s). For use with Stellar SR55 series soft starters. (1) SR55-RJ45-RJ12 adapter and (1) 9.8ft/3m Cat5e cable included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SR55-SPLT>

Technical Specifications

Brand	Stellar
Item	Communication splitter
Series	SR55
Number of Ports	3
Communication Port and Connection Type(s)	(3) RS-485 (RJ45) female
Port Protocol(s)	Modbus RTU
Port Speed(s)	up to 115.2k baud
For Use With	Stellar SR55 series soft starters
Includes	(1) SR55-RJ45-RJ12 adapter and (1) 9.8ft/3m Cat5e cable
Additional Information	Used for creating a Modbus network with multiple SR55 series soft starters

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SR55-SPLT.pdf>
See store item page for other formats.