

# SRA08SS-024.000-SL Cut Sheet



PBC Simplicity 60 Plus series linear precision ground supported shaft, 440C stainless steel, RC50-55, 8-12Ra, 1/2in diameter, 24in length. For use with 1/2in PBC bearings.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SRA08SS-024.000-SL>

## Technical Specifications

<b>Brand</b>	PBC
<b>Item</b>	Shaft
<b>Series</b>	Simplicity 60 Plus
<b>Shaft Type</b>	Linear precision ground supported
<b>Material</b>	440C stainless steel
<b>Hardness</b>	RC50-55
<b>Surface Finish</b>	8-12Ra
<b>Diameter</b>	1/2in
<b>Length</b>	24in
<b>For Use With</b>	1/2in PBC bearings

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SRA08SS-024.000-SL.pdf>  
See store item page for other formats.