

SRA10-036.000-SL Cut Sheet



PBC Simplicity 60 Plus series linear precision ground supported shaft, 1060 steel, RC60-65, 8-12Ra, 5/8in diameter, 36in length. For use with 5/8in PBC bearings.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SRA10-036.000-SL>

Technical Specifications

Brand	PBC
Item	Shaft
Series	Simplicity 60 Plus
Shaft Type	Linear precision ground supported
Material	1060 steel
Hardness	RC60-65
Surface Finish	8-12Ra
Diameter	5/8in
Length	36in
For Use With	5/8in PBC bearings

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SRA10-036.000-SL.pdf>
See store item page for other formats.