

# SRB-22C-5-9.525 Cut Sheet



Sung-II Machinery drive coupling, servo-beam, 7075-T6 aluminum alloy, clamp, size 22, 5 x 9.525mm (3/8in) bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SRB-22C-5-9.525>

## Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	Servo-beam
Material	7075-T6 aluminum alloy
Rated Torque	1 N-m
Maximum Torque	2 N-m
Maximum Angular Misalignment	2.5 degrees
Maximum Parallel Misalignment	0.15mm

Maximum RPM	18000
Attachment Style	Clamp
Coupling Size	22
Bore Diameter	5mm
Bore Diameter 2	3/8in
Outside Diameter	22.2mm
Clamp Screw Fastening Torque	1.7 N-m
Clamp Screw Size	M3

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SRB-22C-5-9.525.pdf>  
See store item page for other formats.