

SRBA-60C-22.22-22.22 Cut Sheet



Sung-II Machinery drive coupling, servo-beam, 7075-T6 aluminum alloy, clamp, size 60, 7/8 x 7/8in bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SRBA-60C-22.22-22.22>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	Servo-beam
Material	7075-T6 aluminum alloy
Rated Torque	30 N·m
Maximum Torque	60 N·m
Maximum Angular Misalignment	2.5 degrees
Maximum Parallel Misalignment	0.25mm
Maximum RPM	7000

Attachment Style	Clamp
Coupling Size	60
Overall Length	76.2mm
Bore Diameter	7/8in
Bore Diameter 2	7/8in
Outside Diameter	60mm
Clamp Screw Fastening Torque	30 N·m
Clamp Screw Size	M8-1.25 x 25mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SRBA-60C-22.22-22.22.pdf>
See store item page for other formats.