

# SS-1002-BR Cut Sheet



CITO StackShort modular manual valve, 2-way, 2-position, glass-filled nylon body, stackable, Cv=26.7. FT-200 temperature gauge included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SS-1002-BR>

## Technical Specifications

<b>Brand</b>	CITO
<b>Item</b>	Valve
<b>Working Fluid</b>	Coolant, oil or water
<b>Valve Type</b>	Manual process
<b>Series</b>	StackShort
<b>Port Quantity</b>	2-way
<b>Number Of Positions</b>	2
<b>Body Material</b>	Glass-filled nylon
<b>Stackable</b>	Yes
<b>Flow Coefficient</b>	26.7
<b>Maximum Operating Pressure</b>	100 psi
<b>Minimum Operating Pressure</b>	0 psi
<b>Working Fluid Temperature</b>	20 to 160 deg F
<b>Form Factor</b>	Modular
<b>Includes</b>	FT-200 temperature gauge

## Agency Approvals

<b>CE</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SS-1002-BR.pdf>  
See store item page for other formats.