

# SS5-0P-4E Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, diffuse, infrared light emission, 200mm sensing distance, selectable light-on/dark-on, PNP, 250 Hz switching frequency, plastic housing, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SS5-0P-4E>

## Technical Specifications

Brand	AutomationDirect	Number of Wires	4
Item	Photoelectric sensor	Switching Output	PNP
Shape	Tubular	Sensing Distance	200mm
Barrel Type	Threaded	Operation Mode	Selectable light-on/dark-on
Housing Size	18mm diameter x 65mm body	Switching Frequency	250 Hz
IP Rating	IP67	Light Emission	Infrared
Housing Material	Plastic	Connection	4-pin M12 quick-disconnect
Sensing Method	Diffuse	Includes	Mounting hardware
Operating Voltage	10-30 VDC	Additional Information	Purchase cable separately

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>