

SS6-0N-4A Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, diffuse, infrared light emission, 400mm sensing distance, selectable light-on/dark-on, NPN, 250 Hz switching frequency, plastic housing, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SS6-0N-4A>

Technical Specifications

Brand	AutomationDirect	Switching Output	NPN
Item	Photoelectric sensor	Sensing Distance	400mm
Shape	Tubular	Operation Mode	Selectable light-on/dark-on
Barrel Type	Threaded	Switching Frequency	250 Hz
Housing Size	18mm diameter x 65mm body	Light Emission	Infrared
IP Rating	IP67	Cable Length	6.5ft/2m
Housing Material	Plastic	Connection	Pigtail
Sensing Method	Diffuse	Conductor Size	22 AWG
Operating Voltage	10-30 VDC	Includes	Mounting hardware
Number of Wires	4		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document