

SS6-0N-4A Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, diffuse, 400mm sensing distance, selectable light-on/dark-on, NPN, 250 Hz switching frequency, 18mm diameter x 65mm body, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SS6-0N-4A>

Technical Specifications

Brand	AutomationDirect
Item	Photoelectric sensor
Shape	Tubular
Barrel Type	Threaded
Housing Size	18mm diameter x 65mm body
IP Rating	IP67
Housing Material	Plastic
Sensing Method	Diffuse
Operating Voltage	10-30 VDC
Number of Wires	4

Switching Output	NPN
Sensing Distance	400mm
Operation Mode	Selectable light-on/dark-on
Switching Frequency	250 Hz
Light Emission	Infrared
Cable Length	6.5ft/2m
Connection	Pigtail
Conductor Size	22 AWG
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document