

SS6-0P-4A Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, diffuse, infrared light emission, 400mm sensing distance, selectable light-on/dark-on, PNP, 250 Hz switching frequency, plastic housing, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SS6-0P-4A>

Technical Specifications

| | |
|--------------------------|---------------------------|
| Brand | AutomationDirect |
| Item | Photoelectric sensor |
| Shape | Tubular |
| Barrel Type | Threaded |
| Housing Size | 18mm diameter x 65mm body |
| IP Rating | IP67 |
| Housing Material | Plastic |
| Sensing Method | Diffuse |
| Operating Voltage | 10-30 VDC |
| Number of Wires | 4 |

| | |
|----------------------------|-----------------------------|
| Switching Output | PNP |
| Sensing Distance | 400mm |
| Operation Mode | Selectable light-on/dark-on |
| Switching Frequency | 250 Hz |
| Light Emission | Infrared |
| Cable Length | 6.5ft/2m |
| Connection | Pigtail |
| Conductor Size | 22 AWG |
| Includes | Mounting hardware |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |