

SSE-00-4A Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, plastic housing, through-beam emitter, 8m sensing distance, 10-30 VDC operating voltage, 2-wire, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SSE-00-4A>

Technical Specifications

Brand	AutomationDirect	Number of Wires	2
Item	Photoelectric sensor	Sensing Distance	8m
Shape	Tubular	Switching Frequency	25 Hz
Barrel Type	Threaded	Light Emission	Infrared
Housing Size	18mm diameter x 65mm body	Cable Length	6.5ft/2m
IP Rating	IP67	Connection	Pigtail
Housing Material	Plastic	Conductor Size	22 AWG
Sensing Method	Through-beam emitter	Includes	Mounting hardware
Operating Voltage	10-30 VDC		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document