

SSE-00-4E Cut Sheet



AutomationDirect photoelectric sensor, tubular, threaded, plastic housing, through-beam emitter, 8m sensing distance, 10-30 VDC operating voltage, 2-wire, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SSE-00-4E>

Technical Specifications

Brand	AutomationDirect	Operating Voltage	10-30 VDC
Item	Photoelectric sensor	Number of Wires	2
Shape	Tubular	Sensing Distance	8m
Barrel Type	Threaded	Switching Frequency	25 Hz
Housing Size	18mm diameter x 65mm body	Light Emission	Infrared
IP Rating	IP67	Connection	4-pin M12 quick-disconnect
Housing Material	Plastic	Includes	Mounting hardware
Sensing Method	Through-beam emitter	Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document