

SSN4201606 Cut Sheet



Wiegmann enclosure, NEMA 4/4X/12/13, 20 x 16 x 6in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, single-door, (4) stainless steel clamps, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SSN4201606>

Technical Specifications

Brand	Wiegmann	Integral Mounting Flange	No
Item	Enclosure	Dual Access	No
Subpanel	Purchase subpanel separately	Knockouts	No
Slope Top	No	Bottom Gland Plate	No
3-Piece Assembly	No	Material	304 stainless steel
Vented	No	Finish	No. 3 intermediate polished
NEMA Rating	4/4X/12/13	Cover Type	Single-door
IP Rating	IP66	Hinge Type	Stainless steel continuous hinge
Nominal Enclosure Dimensions	20 x 16 x 6in (HxWxD)	Number of Hinges Per Door	1
Enclosure Height	20.00in	Latch Type	(4) stainless steel clamps
Enclosure Width	16.00in	Padlock Attachment Type	Padlock hasp and staple
Enclosure Depth	7.03in	Shelf	No
Mounting	Wall	Padlockable	Yes
Integral Mounting Feet	Yes	Keylocking	No

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SSN4201606.pdf>
See store item page for other formats.