

SSN4242408A Cut Sheet



Wiegmann enclosure, NEMA 4/4X/12/13, 24 x 24 x 8in (HxWxD), wall mount, 316L stainless steel, No. 3 intermediate polished finish, single-door, (7) stainless steel clamps, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SSN4242408A>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Wiegmann |
| Item | Enclosure |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| NEMA Rating | 4/4X/12/13 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 24 x 24 x 8in (HxWxD) |
| Enclosure Height | 24.00in |
| Enclosure Width | 24.00in |
| Enclosure Depth | 9.03in |
| Mounting | Wall |
| Integral Mounting Feet | Yes |

| | |
|----------------------------------|----------------------------------|
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Material | 316L stainless steel |
| Finish | No. 3 intermediate polished |
| Cover Type | Single-door |
| Hinge Type | Stainless steel continuous hinge |
| Number of Hinges Per Door | 1 |
| Latch Type | (7) stainless steel clamps |
| Padlock Attachment Type | Padlock hasp and staple |
| Padlockable | Yes |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E64791 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |