

SSN43636123PTW Cut Sheet



Wiegmann enclosure, NEMA 4/4X/12/13, 36 x 36 x 12in (HxWxD), wall mount, 304 stainless steel, white, powder coat finish, single-door, 3-point padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SSN43636123PTW>

Technical Specifications

Brand	Wiegmann	Dual Access	No
Item	Enclosure	Knockouts	No
Subpanel	Purchase subpanel separately	Material	304 stainless steel
Slope Top	No	Color	White
NEMA Rating	4/4X/12/13	Finish	Powder coat
Nominal Enclosure Height	36in	Cover Type	Single-door
Nominal Enclosure Width	36in	Hinge Type	Stainless steel continuous hinge
Nominal Enclosure Depth	12in	Number of Hinges Per Door	1
Mounting	Wall	Latch Type	3-point padlocking handle
Integral Mounting Feet	Yes	Padlockable	Yes
Integral Mounting Flange	No	Keylocking	Yes

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SSN43636123PTW.pdf>
See store item page for other formats.