

# SSN4D6248183PTA Cut Sheet



Wiegmann enclosure, NEMA 4/4X/12, 62 x 48 x 18in (HxWxD), floor mount, 316L stainless steel, No. 3 intermediate polished finish, 2-door, 3-point 316L padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SSN4D6248183PTA>

## Technical Specifications

<b>Brand</b>	Wiegmann
<b>Item</b>	Enclosure
<b>Subpanel</b>	Purchase subpanel separately
<b>Slope Top</b>	No
<b>NEMA Rating</b>	4/4X/12
<b>Nominal Enclosure Height</b>	62in
<b>Nominal Enclosure Width</b>	48in
<b>Nominal Enclosure Depth</b>	18in
<b>Mounting</b>	Floor
<b>Dual Access</b>	No

<b>Knockouts</b>	No
<b>Material</b>	316L stainless steel
<b>Finish</b>	No. 3 intermediate polished
<b>Cover Type</b>	2-door
<b>Hinge Type</b>	Stainless steel continuous hinge
<b>Number of Hinges Per Door</b>	1
<b>Latch Type</b>	3-point 316L padlocking handle
<b>Padlockable</b>	Yes
<b>Keylocking</b>	No

## Agency Approvals

<b>UL Listed File #</b>	E64791
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SSN4D6248183PTA.pdf>  
See store item page for other formats.