

SSN4X423112 Cut Sheet



Wiegmann disconnect enclosure, NEMA 4/4X/12/13, right flange, 42 x 31 x 12in (HxWxD), wall mount, 304 stainless steel, No. 3 intermediate polished finish, single-door, (11) stainless steel clamps, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SSN4X423112>

Technical Specifications

Brand	Wiegmann
Item	Disconnect enclosure
Slope Top	No
NEMA Rating	4/4X/12/13
Disconnect Mounting	Right flange
Nominal Enclosure Height	42in
Nominal Enclosure Width	31.37in
Nominal Enclosure Depth	13.18in
Mounting	Wall
Integral Mounting Feet	Yes
Material	304 stainless steel

Finish	No. 3 intermediate polished
Cover Type	Single-door
Hinge Type	Stainless steel continuous hinge
Number of Hinges Per Door	1
Latch Type	(11) stainless steel clamps
Padlockable	No
Keylocking	No
Subpanel	Purchase subpanel separately
Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SSN4X423112.pdf>
See store item page for other formats.