

SSW050023T2246TPZ Cut Sheet



WEG Electric SSW05 series compact soft starter, 23A, 220/460 VAC at 3-phase, Trip Class 5, rated for 4 start/hour, internally bypassed.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SSW050023T2246TPZ>

Technical Specifications

Brand	WEG Electric	Control Mode	Sinusoidal
Item	Soft starter	Control Power Requirement	90-250 VAC
Controller Type	Compact	Derating	Unit may require derating for applications other than fans and pumps; see specifications for appropriate derating
Series	SSW05	Temperature Rating	0 to 55 deg C
Amperage Rating	23A	Enclosure Type	Enclosed
Nominal Input Voltage	220/460 VAC at 3-phase	Mounting	35mm DIN rail, panel or wall
Nominal Output Voltage	220/460 VAC at 3-phase	Frame Size	1
Trip Class	Trip Class 5	IP Rating	IP00
Starts per Hour	4	Output Frequency Range	50-60 Hz
Internally Bypassed	Yes	Output Type	SCR output
Number of Input Phases	3	Reverse Capability	None
Number of Output Phases	3		
Number of Controlled Output Phases	2		

Agency Approvals

UL Listed File #	E198842
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document