

ST302412LG Cut Sheet



Hammond Eclipse series enclosure, slope top, NEMA 3R/4/12, 30 x 24 x 12in (HxWxD), wall mount, carbon steel, RAL 7035 light gray, powder coat finish, single-door, 1/4-turn semi-flush latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ST302412LG>

Technical Specifications

| | | | |
|-------------------------------------|------------------------------|----------------------------------|---------------------------|
| Brand | Hammond | Integral Mounting Flange | No |
| Item | Enclosure | Dual Access | No |
| Series | Eclipse | Knockouts | No |
| Subpanel | Purchase subpanel separately | Bottom Gland Plate | No |
| Slope Top | Yes | Material | Carbon steel |
| 3-Piece Assembly | No | Color | RAL 7035 light gray |
| Vented | No | Finish | Powder coat |
| NEMA Rating | 3R/4/12 | Cover Type | Single-door |
| IP Rating | IP66 | Hinge Type | Concealed hinges |
| Nominal Enclosure Dimensions | 30 x 24 x 12in (HxWxD) | Number of Hinges Per Door | 3 |
| Enclosure Height | 34.36in | Latch Type | 1/4-turn semi-flush latch |
| Enclosure Width | 24.00in | Number Of Latches | 2 |
| Enclosure Depth | 12.84in | Shelf | No |
| Mounting | Wall | Padlockable | No |
| Integral Mounting Feet | No | Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E65324 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LR21001 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ST302412LG.pdf>
See store item page for other formats.