

ST363612LG Cut Sheet



Hammond Eclipse series enclosure, slope top, NEMA 3R/4/12, 36 x 36 x 12in (HxWxD), wall mount, carbon steel, RAL 7035 light gray, powder coat finish, single-door, 1/4-turn semi-flush latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ST363612LG>

Technical Specifications

Brand	Hammond	Integral Mounting Flange	No
Item	Enclosure	Dual Access	No
Series	Eclipse	Knockouts	No
Subpanel	Purchase subpanel separately	Bottom Gland Plate	No
Slope Top	Yes	Material	Carbon steel
3-Piece Assembly	No	Color	RAL 7035 light gray
Vented	No	Finish	Powder coat
NEMA Rating	3R/4/12	Cover Type	Single-door
IP Rating	IP66	Hinge Type	Concealed hinges
Nominal Enclosure Dimensions	36 x 36 x 12in (HxWxD)	Number of Hinges Per Door	3
Enclosure Height	40.37in	Latch Type	1/4-turn semi-flush latch
Enclosure Width	36.00in	Number Of Latches	2
Enclosure Depth	12.84in	Shelf	No
Mounting	Wall	Padlockable	No
Integral Mounting Feet	No	Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/ST363612LG.pdf>
See store item page for other formats.