

STM14A-L Cut Sheet



Metrol limit switch, stopper, 10mm diameter, smooth, 15.5mm length, 8mm flat head, stainless steel, 3mm plunger, 0.8N contact force, N.O. contact(s), 6.5ft/2m cable length, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/STM14A-L>

Technical Specifications

Brand	Metrol
Item	Limit switch
Switch Type	Stopper
Diameter	10mm
Barrel Type	Smooth
Length	15.5mm
Head Type	8mm flat
Actuator Type	3mm plunger
Contact Force	0.8N
Contact Type	N.O.
Cable Length	6.5ft/2m
Connection	Pigtail
Conductor Size	26 AWG
Stroke	0.5mm
Repeatability	0.01mm
Impact Resistance	0.2 joules
Withstand Load	3000N
Material	Stainless steel
IP Rating	IP44
Operating Temperature	0 to 80 deg C
Indicating Type	LED indication

Agency Approvals

RoHS Status	No
EU REACH	View EU REACH document