

# STP-DRVA-RC-050A Cut Sheet



SureStep regen clamp, 50W, 10-80 VDC, 10 ohm, enclosed. For use with DC input stepper and servo drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/STP-DRVA-RC-050A>

## Technical Specifications

<b>Brand</b>	SureStep
<b>Item</b>	Regen clamp
<b>Power Rating</b>	50W
<b>Voltage Rating</b>	10-80 VDC
<b>Resistance</b>	10 ohm
<b>Enclosure Type</b>	Enclosed
<b>For Use With</b>	DC input stepper and servo drives

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/STP-DRVA-RC-050A.pdf>  
See store item page for other formats.