

STP-LE23-3H09ANN Cut Sheet



SureStep stepper motor linear actuator, external nut, NEMA 23 frame, IP40, triple stack, 3A, 9in lead screw length, 6mm/rev, 12mm lead screw diameter, screw code H, no end machining.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/STP-LE23-3H09ANN>

Technical Specifications

Brand	SureStep	Steps per Revolution	200
Item	Stepper motor linear actuator	Winding Type	Bipolar
Actuator Type	External nut	Screw Code	H
Voltage Type	DC	Driver Type	Lead screw
Motor Type	Brushless	Motor Stack Length	Triple
Number of Input Phases	2	Pitch	3mm
Integrated Brake	No	Screw Lead	6mm/rev
Motor Frame	NEMA 23	Lead Screw Length	9in
IP Rating	IP40	Lead Screw Diameter	12mm
Shaft Type	Single	Number of Thread Starts	2
Amperage Rating	3A	Connector Type	6-position male
Holding Torque Rating	288 oz-in	End Machining	None
Step Angle	1.8-degree	Includes	(1) lead screw flange nut and (1) 1ft motor cable

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document