

STS060A-HT2 Cut Sheet



Metrol limit switch, high temperature, stopper bolt, 6mm diameter, threaded, 1mm pitch, 31.7mm length, 3.4mm flat head, stainless steel, 1.5mm plunger, 1N contact force, (1) N.O. contact(s), 6.5ft/2m cable length, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/STS060A-HT2>

Technical Specifications

Brand	Metrol	Connection	Pigtail
Item	Limit switch	Conductor Size	24 AWG
Application	High temperature	Stroke	0.7mm
Switch Type	Stopper bolt	Repeatability	0.01mm
Diameter	6mm	Impact Resistance	0.4 joules
Barrel Type	Threaded	Withstand Load	5000N
Length	31.7mm	Thread Pitch	1mm
Head Type	3.4mm flat	Material	Stainless steel
Actuator Type	1.5mm plunger	Head Material	Stainless steel
Contact Force	1N	IP Rating	IP65
Contact Type	(1) N.O.	Operating Temperature	0 to 80 deg C
Cable Length	6.5ft/2m	Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/STS060A-HT2.pdf>
See store item page for other formats.