

SV2A-4040 Cut Sheet



SureServo2 servo drive, 400W, 460 VAC, 3-phase, (1) RS-485 (RJ45) port(s), Modbus RTU and Modbus ASCII. For use with 400W systems. Optional EtherNet/IP and Modbus TCP cards available.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SV2A-4040>

Technical Specifications

Brand	SureServo2
Item	Servo drive
Voltage Type	AC
Amperage Rating	1.5A
Power Rating	400W
Nominal Input Voltage	460 VAC
Number of Input Phases	3
Output Type	SVPWM output
Steps per Revolution	Up to 24-bit (16777216 ppr)
Encoder Output	Yes
Encoder Resolution	24-bit (16777216 ppr)
Communication Port and Connection Type(s)	(1) RS-485 (RJ45)
Port Protocol(s)	<ul style="list-style-type: none">• Modbus RTU Slave• Modbus ASCII Slave
Port Speed(s)	up to 115.2k baud
Temperature Rating	0 to 55 deg C
Enclosure Type	Enclosed
IP Rating	IP20
Mounting	Panel
Control Mode	Torque, velocity and position
Command Signal(s)	<ul style="list-style-type: none">• step and direction• CW/CCW• A/B Quad• internal indexing (via discrete input and communication port)• torque and velocity (via analog input)
Number of Discrete Input Points	10
Discrete Input Type	Sinking/sourcing
Number of Discrete Output Points	6
Discrete Output Type	Sinking/sourcing
Number of Analog Input Channels	2
Analog Input Signal Type	Voltage

Input Voltage Signal Range	+/- 10 VDC
Number of Analog Output Channels	2
Analog Output Signal Type	Voltage
Output Voltage Signal Range	+/- 8 VDC
Tuning Mode	Easy/auto (4 methods)/manual
Protection Type(s)	<ul style="list-style-type: none">• overcurrent• overvoltage• undervoltage• over-temperature• regeneration error• overload• velocity/position error• encoder error• secondary encoder position error• communication error• short circuit
Configuration	Software and keypad
For Use With	400W systems
Additional Information	Optional EtherNet/IP and Modbus TCP cards available

SV2A-4040 Cut Sheet

Agency Approvals

UL Listed File #	E198015
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SV2A-4040.pdf>
See store item page for other formats.
