

SV2C-PC12-03FN Cut Sheet



SureServo2 power flex cable, mating connectors, 9.8ft/3m cable length. For use with 230 VAC 1 kW medium inertia and 1.5 kW SureServo2 motors without brake.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SV2C-PC12-03FN>

Technical Specifications

Brand	SureServo2
Item	Flex cable
Cable Type	Power
Cable Length	9.8ft/3m
For Use With	230 VAC 1 kW medium inertia and 1.5 kW SureServo2 motors without brake
Additional Information	Some SV2C-PC12-xxxx cables are manufactured with fork terminals. If used with SV2A-2150 remove the U, V and W forks and strip the insulation back far enough to insert into the drive's spring cage terminals. Tinning the leads is recommended

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SV2C-PC12-03FN.pdf>
See store item page for other formats.