

# SV2C-PC12-10NB Cut Sheet



SureServo2 power cable, mating connectors, 32.8ft/10m cable length. For use with 230 VAC 1 kW medium inertia and 1.5 kW SureServo2 motors with brake.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SV2C-PC12-10NB>

## Technical Specifications

Brand	SureServo2
Item	Cable
Cable Type	Power
Cable Length	32.8ft/10m
For Use With	230 VAC 1 kW medium inertia and 1.5 kW SureServo2 motors with brake
Additional Information	Some SV2C-PC12-xxxx cables are manufactured with fork terminals. If used with SV2A-2150 remove the U, V and W forks and strip the insulation back far enough to insert into the drive's spring cage terminals. Tinning the leads is recommended

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SV2C-PC12-10NB.pdf>  
See store item page for other formats.