

SV2C-PD12-03NB Cut Sheet



SureServo2 power cable, mating connectors, 9.8ft/3m cable length. For use with 230 VAC 2 kW and 3 kW and 460 VAC 3 kW SureServo2 motors with brake.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SV2C-PD12-03NB>

Technical Specifications

| | |
|------------------------|--|
| Brand | SureServo2 |
| Item | Cable |
| Cable Type | Power |
| Cable Length | 9.8ft/3m |
| For Use With | 230 VAC 2 kW and 3 kW and 460 VAC 3 kW SureServo2 motors with brake |
| Additional Information | Some SV2C-PD12-xxxx cables are manufactured with fork terminals. If used with SV2A-2200 or SV2A-2300 remove the U, V and W forks and strip the insulation back far enough to insert into the drive's spring cage terminals. Tinning the leads is recommended |

Agency Approvals

| | |
|----------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SV2C-PD12-03NB.pdf>
See store item page for other formats.