

SV2C-PD12-10FN Cut Sheet



SureServo2 power flex cable, mating connectors, 32.8ft/10m cable length. For use with 230 VAC 2 kW and 3 kW and 460 VAC 3 kW SureServo2 motors without brake.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SV2C-PD12-10FN>

Technical Specifications

Brand	SureServo2
Item	Flex cable
Cable Type	Power
Cable Length	32.8ft/10m
For Use With	230 VAC 2 kW and 3 kW and 460 VAC 3 kW SureServo2 motors without brake
Additional Information	Some SV2C-PD12-xxxx cables are manufactured with fork terminals. If used with SV2A-2200 or SV2A-2300 remove the U, V and W forks and strip the insulation back far enough to insert into the drive's spring cage terminals. Tinning the leads is recommended

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	RoHS Statement