

SV2C-PD12-20NN Cut Sheet



SureServo2 power cable, mating connectors, 65.6ft/20m cable length. For use with 230 VAC 2 kW and 3 kW and 460 VAC 3 kW SureServo2 motors without brake.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SV2C-PD12-20NN>

Technical Specifications

Brand	SureServo2
Item	Cable
Cable Type	Power
Cable Length	65.6ft/20m
For Use With	230 VAC 2 kW and 3 kW and 460 VAC 3 kW SureServo2 motors without brake
Additional Information	Some SV2C-PD12-xxxx cables are manufactured with fork terminals. If used with SV2A-2200 or SV2A-2300 remove the U, V and W forks and strip the insulation back far enough to insert into the drive's spring cage terminals. Tinning the leads is recommended

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SV2C-PD12-20NN.pdf>
See store item page for other formats.