

SVU12M Cut Sheet



NITRA pneumatic push-to-connect fitting, union straight stop valve, thermoplastic (PBT) body, (2) 12mm tube connection(s). Package of 5.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SVU12M>

Technical Specifications

Brand	NITRA
Item	Pneumatic Push-to-connect Fitting
Fitting Type	Union straight stop valve
Body Material	Thermoplastic (PBT)
Thread Sealant	No
Connection	(2) 12mm push-to-connect
Operating Pressure	-29.5in Hg to 150 psi
Operating Temperature	32 to 140 deg F
Quantity per Pack	5
For Use With	Flexible pneumatic tubing

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document