T1105K0220C Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com



ACME general purpose transformer, encapsulated core, 1.5 kVA, 1-phase, 120–277 VAC selectable, 120/240 VAC secondary, 60 Hz, NEMA 3R, wall mount.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/T1105K0220C

Technical Specifications

Brand	ACME
Item	Transformer
Transformer Type	General purpose
Core Type	Encapsulated
Power Rating	1.5 kVA
Number of Phases	1
Primary Voltage	120/208/240/277 VAC
Secondary Voltage	120/240 VAC
Frequency	60 Hz
Fused	No
Electrostatic Shield	No
NEMA Rating	3R
Mounting	Wall
Connection	Pigtail

Agency Approvals

UL Listed File #	E79947 Style SR
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/T1105K0220C.pdf
See store item page for other formats.