

T111685 Cut Sheet



ACME buck-boost transformer, encapsulated core, 2 kVA, 1-phase, 120/240 VAC primary, 12/24 VAC secondary, 60 Hz, NEMA 3R, wall mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T111685>

Technical Specifications

| | |
|-----------------------------|---|
| Brand | ACME |
| Item | Transformer |
| Transformer Type | Buck-boost |
| Core Type | Encapsulated |
| Power Rating | 2 kVA |
| Number of Phases | 1 |
| Primary Voltage | 120/240 VAC |
| Secondary Voltage | 12/24 VAC |
| Frequency | 60 Hz |
| Electrostatic Shield | No |
| NEMA Rating | 3R |
| Mounting | Wall |
| Application | Suitable for use as isolation transformer in 1-Phase applications or an auto transformer in 1-Phase or 3-Phase applications |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E79947 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |