

# T111687 Cut Sheet



ACME buck-boost transformer, encapsulated core, 5 kVA, 1-phase, 120/240 VAC primary, 12/24 VAC secondary, 60 Hz, NEMA 3R, wall mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T111687>

## Technical Specifications

Brand	ACME
Item	Transformer
Transformer Type	Buck-boost
Core Type	Encapsulated
Power Rating	5 kVA
Number of Phases	1
Primary Voltage	120/240 VAC
Secondary Voltage	12/24 VAC
Frequency	60 Hz

Fused	No
Electrostatic Shield	No
NEMA Rating	3R
Mounting	Wall
Connection	Pigtail
Application	Suitable for use as isolation transformer in 1-Phase applications or an auto transformer in 1-Phase or 3-Phase applications

## Agency Approvals

UL Listed File #	E79947
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/T111687.pdf>  
See store item page for other formats.