

# T113073 Cut Sheet



ACME buck-boost transformer, encapsulated core, 1 kVA, 1-phase, 120/240 VAC primary, 16/32 VAC secondary, 60 Hz, NEMA 3R, wall mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T113073>

## Technical Specifications

<b>Brand</b>	ACME
<b>Item</b>	Transformer
<b>Transformer Type</b>	Buck-boost
<b>Core Type</b>	Encapsulated
<b>Power Rating</b>	1 kVA
<b>Number of Phases</b>	1
<b>Primary Voltage</b>	120/240 VAC
<b>Secondary Voltage</b>	16/32 VAC
<b>Frequency</b>	60 Hz

<b>Fused</b>	No
<b>Electrostatic Shield</b>	No
<b>NEMA Rating</b>	3R
<b>Mounting</b>	Wall
<b>Connection</b>	Pigtail
<b>Application</b>	Suitable for use as isolation transformer in 1-Phase applications or an auto transformer in 1-Phase or 3-Phase applications

## Agency Approvals

<b>UL Listed File #</b>	E79947
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/T113073.pdf>  
See store item page for other formats.