

T113075 Cut Sheet



ACME buck-boost transformer, encapsulated core, 2 kVA, 1-phase, 120/240 VAC primary, 16/32 VAC secondary, 60 Hz, NEMA 3R, wall mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T113075>

Technical Specifications

Brand	ACME	Fused	No
Item	Transformer	Electrostatic Shield	No
Transformer Type	Buck-boost	NEMA Rating	3R
Core Type	Encapsulated	Mounting	Wall
Power Rating	2 kVA	Connection	Pigtail
Number of Phases	1	Application	Suitable for use as isolation transformer in 1-Phase applications or an auto transformer in 1-Phase or 3-Phase applications
Primary Voltage	120/240 VAC		
Secondary Voltage	16/32 VAC		
Frequency	60 Hz		

Agency Approvals

UL Listed File #	E79947
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/T113075.pdf>
See store item page for other formats.