

# T137923 Cut Sheet



ACME buck-boost transformer, encapsulated core, 3 kVA, 1-phase, 240/480 VAC primary, 24/48 VAC secondary, 60 Hz, NEMA 3R, wall mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T137923>

## Technical Specifications

|                          |              |
|--------------------------|--------------|
| <b>Brand</b>             | ACME         |
| <b>Item</b>              | Transformer  |
| <b>Transformer Type</b>  | Buck-boost   |
| <b>Core Type</b>         | Encapsulated |
| <b>Power Rating</b>      | 3 kVA        |
| <b>Number of Phases</b>  | 1            |
| <b>Primary Voltage</b>   | 240/480 VAC  |
| <b>Secondary Voltage</b> | 24/48 VAC    |
| <b>Frequency</b>         | 60 Hz        |

|                             |   |
|-----------------------------|---|
| <b>Fused</b>                | No  |
| <b>Electrostatic Shield</b> | No  |
| <b>NEMA Rating</b>          | 3R  |
| <b>Mounting</b>             | Wall  |
| <b>Connection</b>           | Pigtail   |
| <b>Application</b>          | Suitable for use as isolation transformer in 1-Phase applications or an auto transformer in 1-Phase or 3-Phase applications |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E79947                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/T137923.pdf>  
See store item page for other formats.