

T181065 Cut Sheet



ACME buck-boost transformer, encapsulated core, 500 VA, 1-phase, 240/480 VAC primary, 24/48 VAC secondary, 50/60 Hz, NEMA 3R, wall mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T181065>

Technical Specifications

Brand	ACME
Item	Transformer
Transformer Type	Buck-boost
Core Type	Encapsulated
Power Rating	500 VA
Number of Phases	1
Primary Voltage	240/480 VAC
Secondary Voltage	24/48 VAC
Frequency	50/60 Hz

Fused	No
Electrostatic Shield	No
NEMA Rating	3R
Mounting	Wall
Connection	Pigtail
Application	Suitable for use as isolation transformer in 1-Phase applications or an auto transformer in 1-Phase or 3-Phase applications

Agency Approvals

UL Listed File #	E79947
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/T181065.pdf>
See store item page for other formats.