

# T2236CH Cut Sheet

Wiegmann wiring trough, 2.5 x 2.5 x 36in (HxDxL), NEMA 4, carbon steel, ANSI 61 gray, powder coat finish, single-door.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T2236CH>

## Technical Specifications

|                               |                     |
|-------------------------------|---------------------|
| <b>Brand</b>                  | Wiegmann            |
| <b>Item</b>                   | Wiring trough       |
| <b>NEMA Rating</b>            | 4                   |
| <b>Enclosure Height</b>       | 2.72in              |
| <b>Enclosure Depth</b>        | 2.75in              |
| <b>Enclosure Length</b>       | 36.31in             |
| <b>Integral Mounting Feet</b> | Yes                 |
| <b>Knockouts</b>              | No                  |
| <b>Material</b>               | Carbon steel        |
| <b>Color</b>                  | ANSI 61 gray        |
| <b>Finish</b>                 | Powder coat         |
| <b>Cover Type</b>             | Single-door         |
| <b>Latch Type</b>             | Plated steel clamps |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E32576                                 |
| <b>UL Recognized File #</b> | N/A                                    |
| <b>UL Hazardous File #</b>  | N/A                                    |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | N/A                                    |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |