

# T242410RT Cut Sheet



AttaBox Triton series enclosure, NEMA 1/3R, 24 x 24 x 10in (HxWxD), wall mount, fiberglass reinforced polyester, gray, single-door, (2) twist-lock latches, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T242410RT>

## Technical Specifications

|                                 |                              |
|---------------------------------|------------------------------|
| <b>Brand</b>                    | AttaBox                      |
| <b>Item</b>                     | Enclosure                    |
| <b>Series</b>                   | Triton                       |
| <b>Subpanel</b>                 | Purchase subpanel separately |
| <b>Slope Top</b>                | No                           |
| <b>NEMA Rating</b>              | 1/3R                         |
| <b>Nominal Enclosure Height</b> | 24in                         |
| <b>Nominal Enclosure Width</b>  | 24in                         |
| <b>Nominal Enclosure Depth</b>  | 10in                         |
| <b>Mounting</b>                 | Wall                         |
| <b>Integral Mounting Feet</b>   | Yes                          |
| <b>Integral Mounting Flange</b> | No                           |

|                                  |                                 |
|----------------------------------|---------------------------------|
| <b>Dual Access</b>               | No                              |
| <b>Knockouts</b>                 | No                              |
| <b>Material</b>                  | Fiberglass reinforced polyester |
| <b>Color</b>                     | Gray                            |
| <b>Cover Type</b>                | Single-door                     |
| <b>Hinge Type</b>                | Continuous hinge                |
| <b>Number of Hinges Per Door</b> | 1                               |
| <b>Latch Type</b>                | (2) twist-lock latches          |
| <b>Padlock Attachment Type</b>   | Padlock hasp and staple         |
| <b>Padlockable</b>               | Yes                             |
| <b>Keylocking</b>                | No                              |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E64358                                 |
| <b>UL Recognized File #</b> | none                                   |
| <b>UL Hazardous File #</b>  | none                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | LR069014                               |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/T242410RT.pdf>  
See store item page for other formats.