

T253009S Cut Sheet



ACME general purpose transformer, encapsulated core, 750 VA, 1-phase, 240/480 VAC primary, 120/240 VAC secondary, 50/60 Hz, electrostatic shield, NEMA 3R, wall mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T253009S>

Technical Specifications

Brand	ACME
Item	Transformer
Transformer Type	General purpose
Core Type	Encapsulated
Power Rating	750 VA
Number of Phases	1
Primary Voltage	240/480 VAC
Secondary Voltage	120/240 VAC
Frequency	50/60 Hz
Fused	No
Electrostatic Shield	Yes
NEMA Rating	3R
Mounting	Wall
Connection	Pigtail

Agency Approvals

UL Listed File #	E79947
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/T253009S.pdf>
See store item page for other formats.