

T292E41 Cut Sheet



RuB T292 potable water manual ball valve, 2-port (2-way), 2-position, lead-free brass body, PTFE seal(s), 3/4in female NPT inlet(s), 3/4in female NPT outlet(s), Cv=48.5, NSF 61 and ANSI 61.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T292E41>

Technical Specifications

| | |
|----------------------------|-----------------|
| Brand | RuB |
| Item | Valve |
| Working Fluid | Potable water |
| Valve Type | Manual ball |
| Series | T292 |
| Port Quantity | 2-port (2-way) |
| Number Of Positions | 2 |
| Operator Type | Rotary lever |
| Body Material | Lead-free brass |

| | |
|-------------------------------------|--------------------|
| Seal Material | PTFE |
| Inlet Port | 3/4in female NPT |
| Outlet Port | 3/4in female NPT |
| Flow Coefficient | 48.5 |
| Minimum Operating Pressure | 0 psi |
| Maximum Operating Pressure | 600 psi |
| Working Fluid Temperature | -40 to +350 °F |
| Potable Water Certifications | NSF 61 and ANSI 61 |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | 112439 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/T292E41.pdf>
See store item page for other formats.