

T292H41 Cut Sheet



RuB T292 potable water manual ball valve, 2-port (2-way), 2-position, lead-free brass body, PTFE seal(s), 1-1/2in female NPT inlet(s), 1-1/2in female NPT outlet(s), Cv=144.4, NSF 61 and ANSI 61.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T292H41>

Technical Specifications

Brand	RuB
Item	Valve
Working Fluid	Potable water
Valve Type	Manual ball
Series	T292
Port Quantity	2-port (2-way)
Number Of Positions	2
Operator Type	Rotary lever
Body Material	Lead-free brass

Seal Material	PTFE
Inlet Port	1-1/2in female NPT
Outlet Port	1-1/2in female NPT
Flow Coefficient	144.4
Minimum Operating Pressure	0 psi
Maximum Operating Pressure	600 psi
Working Fluid Temperature	-40 to +350 °F
Potable Water Certifications	NSF 61 and ANSI 61

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	112439
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/T292H41.pdf>
See store item page for other formats.