

# T2R-M1-ADJ-240U Cut Sheet



ProSense multi-mode relay timer, 0.1 seconds to 100 minutes selectable timing range, 24-240 VAC and 12-125 VDC operating voltage, 10A contact rating, (1) SPDT timed relay output(s), surface mount, 1/4in male quick-connect terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T2R-M1-ADJ-240U>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Relay timer
<b>Timer Type</b>	Multi-mode
<b>Timing Range</b>	0.1 seconds to 100 minutes selectable
<b>Operating Voltage</b>	24-240 VAC and 12-125 VDC
<b>Timer Output Type(s)</b>	(1) SPDT timed relay
<b>Timer Function(s)</b>	<ul style="list-style-type: none"><li>• on-delay</li><li>• off-delay</li><li>• on-interval</li><li>• single-shot</li></ul>
<b>Contact Rating</b>	10A
<b>Mounting</b>	Surface
<b>Connector Type</b>	1/4in male quick-connect terminal

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E191059
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/T2R-M1-ADJ-240U.pdf>  
See store item page for other formats.