

T2R-M1-ADJ-240U Cut Sheet



ProSense multi-mode relay timer, 0.1 seconds to 100 minutes selectable timing range, 24-240 VAC and 12-125 VDC operating voltage, 10A contact rating, (1) SPDT timed relay output(s), surface mount, 1/4in male quick-connect terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T2R-M1-ADJ-240U>

Technical Specifications

Brand	ProSense
Item	Relay timer
Timer Type	Multi-mode
Timing Range	0.1 seconds to 100 minutes selectable
Operating Voltage	24-240 VAC and 12-125 VDC
Timer Output Type(s)	(1) SPDT timed relay
Timer Function(s)	<ul style="list-style-type: none">• on-delay• off-delay• on-interval• single-shot
Contact Rating	10A
Mounting	Surface
Connector Type	1/4in male quick-connect terminal

Agency Approvals

UL Listed File #	None
UL Recognized File #	E191059
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document