

# T2R-M3-ADJ-240U Cut Sheet



ProSense multi-mode relay timer, 0.1 seconds to 1,000 minutes selectable timing range, 24-240 VAC and 12-125 VDC operating voltage, 10A contact rating, (1) SPDT timed relay output(s), surface mount, 1/4in male quick-connect terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T2R-M3-ADJ-240U>

## Technical Specifications

|                             |  |
|-----------------------------|--|
| <b>Brand</b>                | ProSense   |
| <b>Item</b>                 | Relay timer  |
| <b>Timer Type</b>           | Multi-mode   |
| <b>Timing Range</b>         | 0.1 seconds to 1,000 minutes selectable  |
| <b>Operating Voltage</b>    | 24-240 VAC and 12-125 VDC  |
| <b>Timer Output Type(s)</b> | (1) SPDT timed relay   |
| <b>Timer Function(s)</b>    | <ul style="list-style-type: none"><li>• on-repeat cycle</li><li>• off-repeat cycle</li><li>• delayed interval</li><li>• delayed interval triggered</li></ul> |
| <b>Contact Rating</b>       | 10A  |
| <b>Mounting</b>             | Surface  |
| <b>Connector Type</b>       | 1/4in male quick-connect terminal  |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E191059                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |