

T2R-SST-32-24AD Cut Sheet



ProSense fleeting (single-shot) relay timer, 0.1 to 10 minutes timing range, 24 VAC/VDC operating voltage, 10A contact rating, (1) SPDT timed relay output(s), surface mount, 1/4in male quick-connect terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T2R-SST-32-24AD>

Technical Specifications

Brand	ProSense
Item	Relay timer
Timer Type	Fleeting (single-shot)
Timing Range	0.1 to 10 minutes
Operating Voltage	24 VAC/VDC
Timer Output Type(s)	(1) SPDT timed relay
Timer Function(s)	fleeting (single-shot)
Contact Rating	10A
Mounting	Surface
Connector Type	1/4in male quick-connect terminal

Agency Approvals

UL Listed File #	None
UL Recognized File #	E191059
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/T2R-SST-32-24AD.pdf>
See store item page for other formats.