

# T2S-FD-30-240A Cut Sheet



ProSense off-delay relay timer, 0.1 to 10 seconds timing range, 24-240 VAC operating voltage, 1A contact rating, (1) SPNO timed solid state relay output(s), surface mount, 1/4in male quick-connect terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T2S-FD-30-240A>

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Relay timer
<b>Timer Type</b>	Off-delay
<b>Timing Range</b>	0.1 to 10 seconds
<b>Operating Voltage</b>	24-240 VAC
<b>Timer Output Type(s)</b>	(1) SPNO timed solid state relay
<b>Timer Function(s)</b>	off-delay
<b>Contact Rating</b>	1A
<b>Mounting</b>	Surface
<b>Connector Type</b>	1/4in male quick-connect terminal

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E222847
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>