

# T2S-FD-32-125D Cut Sheet



ProSense off-delay relay timer, 0.1 to 10 minutes timing range, 12-125 VDC operating voltage, 1A contact rating, (1) SPNO timed solid state relay output(s), surface mount, 1/4in male quick-connect terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T2S-FD-32-125D>

## Technical Specifications

|                             |                                   |
|-----------------------------|-----------------------------------|
| <b>Brand</b>                | ProSense                          |
| <b>Item</b>                 | Relay timer                       |
| <b>Timer Type</b>           | Off-delay                         |
| <b>Timing Range</b>         | 0.1 to 10 minutes                 |
| <b>Operating Voltage</b>    | 12-125 VDC                        |
| <b>Timer Output Type(s)</b> | (1) SPNO timed solid state relay  |
| <b>Timer Function(s)</b>    | off-delay                         |
| <b>Contact Rating</b>       | 1A                                |
| <b>Mounting</b>             | Surface                           |
| <b>Connector Type</b>       | 1/4in male quick-connect terminal |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E222847                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |