

# T30-N40160-25C Cut Sheet



ProSense bi-metal dial thermometer, 3in diameter, 2-1/2in insertion length, -40 to 160 deg F/-40 to 70 deg C, 1/2in male NPT process connection, center back mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/T30-N40160-25C>

---

## Technical Specifications

<b>Brand</b>	ProSense
<b>Item</b>	Bi-metal dial thermometer
<b>Diameter</b>	3in
<b>Insertion Length</b>	2 1/2in
<b>Scale</b>	-40 to 160 deg F/-40 to 70 deg C
<b>Process Connection</b>	1/2in male NPT
<b>Mounting</b>	Center back

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>